



Dymax

Product Name:

Dymax ZIP™ Shutter for 2000-EC & 5000-EC UV Curing Flood Lamps

Manufacturer Part Number:

37863



Click here for more details on the Dymax ZIP™ Shutter for 2000-EC & 5000-EC UV Curing Flood Lamps

- · Powerful UV light-curing lamps (up to 225 mW/cm²)
- Two bulb options (shortwave or longwave)
- Large curing area 5" x 5" (12.7 cm x 12.7 cm) or 8" x 8" (20.3 cm x 20.3 cm)
- · Adjustable lamp height
- Typical cure times of 5-30 seconds
- · Bulbs are warranted for 2,000 hours
- · Shutter that can be actuated by foot pedal or PLC
- · 100% shielding with safety interlock available

2000-EC & 5000-EC

UV Light-Curing Flood Systems

Dymax UV light-curing flood lamps offer moderate to high intensity UV lightcuring over a 5" x 5" or 8" x 8" area. Curing in 5-30 seconds is typical using Dymax light-curable adhesives. These lamps are available with or without shutters and shielding and are simple to operate. Dymax UV flood lamps can be used as bench-top curing systems or easily integrated into automated assembly systems. These flood lamps offer the industry's most consistent intensity over the 2,000 hour bulb warranty.

2000-EC and 5000-EC UV Light-Curing Flood Lamps

The 2000-EC and 5000-EC modular UV light-curing flood lamps offer moderate to high intensity over a large area (up to 8" x 8"). By adding shielding and/or shutters, these UV light-curing flood lamps can be used as either turnkey bench-top systems or integrated into an automated assembly process. Either lamp may be fitted with bulbs that produce primarily shortwave UV, primarily longwave UV, or primarily visible light.



2000-EC modular power supply and housing, 8" x 8" curing area



5000-EC modular power supply and housing, 5" x 5" curing area





Dymax

Product Name:


Dymax ZIP™ Shutter for 2000-EC & 5000-EC UV Curing Flood Lamps

Manufacturer Part Number:


37863

Click here for more details on the Dymax ZIP™ Shutter for 2000-EC & 5000-EC UV Curing Flood Lamps

| Specifications | 2000-EC Modular | 5000-EC Modular | |
|---|---|--|--|
| Part Number | 38105 | 38100 | |
| Initial Intensity* | 105 mW/cm ² | 225 mW/cm ² | |
| Curing Area | 8" x 8" (20.3 cm x 20.3 cm) | 5" x 5" (12.7 cm x 12.7 cm) | |
| Working Distance | 2" - 6" | 2" - 6" | |
| Reflector Housing Dimensions (L x W x H) | 9" x 10.5" x 7.5" (22.9 cm x 26.7 cm x 19.1 cm) | 6.75" x 6.75" x 8" (17.2 cm x 17.2 cm x 20.3 cm) | |
| Power Supply Dimensions (L x W x H) | 12" x 16" x 4.25" (30.5 cm x 40.6 cm x 10.8 cm) | | |
| Bulb Warranty | 2,000 hours | | |
| Typical Degradation | < 20% over 2,000 hours | | |
| Power Requirements | 90-265V, 50-60 Hz | | |
| Replacement Bulb Part Numbers | 38560 Metal Halide (Standard, UVA, Longwave) 36970 Mercury (UVB, Shortwave) 36658 Visible | | |



EC Flood Lamp Spectral Output



The intensity generated by Dymax flood systems is very consistent. With continuous use, bulb degradation of less the 20% over the first 2,000 hours is typical. On/off cycles will accelerate bulb degradation.

Contact the professionals at Fiber Optic Center for a quote or to get more details.





Dymax

Product Name:

Dymax ZIP™ Shutter for 2000-EC & 5000-EC UV Curing Flood Lamps

Manufacturer Part Number:

37863


Click here for more details on the Dymax ZIP™ Shutter for 2000-EC & 5000-EC UV Curing Flood Lamps


Accessories

Shutters

Dymax UV light-curing flood lamps require a five (5) minute warm up and five (5) minutes to cool down. For that reason, it is not practical to control exposure by turning lamps on/off. Shutters, however, can be used to control exposure time. Dymax offers the following shutters for use with the 2000-EC and 5000-EC UV-curing flood systems.







| ZIP [™] Shutter | | | |
|--|--|--|--|
| Part Number 37863 38071 - Replacement Curtain | | | |
| Dimensions (L x W x H) | 13.5" x 11.8" x 4.5" (34.3 cm x 29.9 cm x 11.4 cm) | | |
| Description | Electronic, curtain-style shutter. Actuated via finger switch, foot pedal, or customer supplied switch (or PLC). | | |





Dymax

Product Name:

Dymax ZIP™ Shutter for 2000-EC & 5000-EC UV Curing Flood Lamps

Manufacturer Part Number:

37863

Click here for more details on the Dymax ZIP™ Shutter for 2000-EC & 5000-EC UV Curing Flood Lamps

Shielding

Dymax offers two shielding options for its UV curing flood systems, a mounting stand kit and a Light Shield.







| Light Shield | | |
|-----------------------------------|--|--|
| Part Number | 41175 | |
| Inside Dimensions (L x W x H) | 14.9" x 10.6" x 8.0" (37.9 cm x 26.9 cm x 20.3 cm) | |
| Outside Dimensions (L x W x H) | 16.9" x 12.6" x 10.8" (42.9 cm x 32 cm x 27.4 cm) | |
| Description | 360° shielding. Swing up door and slide out shelf. Compatible with Dymax shutters. | |





Dymax

Product Name:

Dymax ZIP™ Shutter for 2000-EC & 5000-EC UV Curing Flood Lamps

Manufacturer Part Number:

37863

Click here for more details on the Dymax ZIP™ Shutter for 2000-EC & 5000-EC UV Curing Flood Lamps

| Part Numbers for Various Lamp/Shutter/Shielding Combinations | 2000-EC | 5000-EC |
|--|---------|---------|
| Modular (no shielding or shutter) | 38105 | 38100 |
| With Mounting Stand | 39730 | 39830 |
| With Light Shield | 39720 | 39820 |
| With Light Shield and Manual Shutter | 39723 | 39823 |
| With Light Shield and ZIP™ Shutter | 39721 | 39821 |



The ACCU-CAL™ 50 radiometer is simple to operate and offers repeatable measurement of UV light. The Dymax ACCU-CAL™ 50 can measure UV light emitted from lightguides (3 mm, 5 mm, and 8 mm), UV flood systems, and UV conveyors.

©2018-2021 Dymax Corporation. All rights reserved. All trademarks in this guide, except where noted, are the property of, or used under license by, Dymax Corporation, U.S.A.

Please note that most light-curing system applications are unique. Dymax does not warrant the fitness of the product for the intended application. Any warranty applicable to the product, its application and use is strictly limited to that contained in Dymax standard Conditions of Sale published on our website. Dymax recommends that any intended application be evaluated and tested by the user to ensure that desired performance criteria are satisfied.

PB071 6/8/2021

Contact the professionals at Fiber Optic Center for a quote or to get more details.